

ICs

Qty. Description

Amplifiers

- 1 AD8226 instrumentation amplifier (BOB*)
- 1 ADTL082 JFET op amp (BOB)
- 1 AD8541 CMOS rail-to-rail op amp (BOB)
- 2 OP482 high speed JFET op amp (PDIP)
- 2 OP484 precision rail-to-rail I/O op amp (PDIP)
- 2 OP27 low noise, precision op amp (PDIP)
- 2 OP37 precision op amp (PDIP)
- 2 OP97 low power, high precision op amp (PDIP)

Sensors

- 1 AD8210 current shunt monitor (BOB)
- 1 AD22151 magnetic field sensor (BOB)
- 1 ADXL327 3-axis accelerometer (BOB)
- 2 AD22100 voltage temperature sensor (TO-92)
- 1 AD592 current temperature sensor (TO-92)
- 1 TMP01 temperature controller (PDIP)
- 1 MCE-100 electret microphone
- 1 QSC114 infrared transistor
- 1 B57164K103J 10 k Ω thermistor

Misc ICs

- 1 AD584 programmable V_{REF} (PDIP)
- 1 AD654 voltage-to-frequency converter (PDIP)
- 2 AD8561 comparator (PDIP)
- 1 ADP3300 LDO linear regulator (BOB)
- 1 SSM2220 PNP matched transistor (BOB)
- 1 SSM2212 NPN matched transistor (BOB)

*Breakout board

RoHS Compliant

Resistors

Qty. Description

- 1 6.2 Ω (10 W)
- 5 1.1 Ω
- 5 10 Ω
- 5 47 Ω
- 5 68 Ω
- 5 100 Ω
- 5 470 Ω
- 5 1 k Ω
- 5 1.5 k Ω
- 5 2.2 k Ω
- 5 4.7 k Ω
- 5 6.8 k Ω
- 5 10 k Ω
- 5 20 k Ω
- 5 47 k Ω
- 5 68 k Ω
- 5 100 k Ω
- 5 200 k Ω
- 5 470 k Ω
- 5 1 M Ω
- 5 5 M Ω

Potentiometers

Qty. Description

- 1 5 k Ω
- 2 10 k Ω
- 1 50 k Ω

Capacitors

Qty. Description

- 2 39 pF
- 2 100 pF
- 2 0.001 μ F
- 2 0.0047 μ F
- 2 0.01 μ F
- 2 0.047 μ F
- 2 0.1 μ F
- 2 1 μ F
- 2 4.7 μ F
- 2 10 μ F
- 2 22 μ F
- 2 47 μ F
- 1 220 μ F

Transistors

Qty. Description

- 3 2N3904
- 3 2N3906
- 1 CD4007
- 1 IRF510
- 1 TIP31CFS
- 1 TIP32CFS
- 1 ZVN2110A
- 2 ZVN3310
- 2 ZVP2110A

LEDs

Qty. Description

- 2 Green
- 2 Orange
- 2 Red
- 1 QED123 infrared LED

Diodes

Qty. Description

- 1 1N3064
- 1 1N4001
- 1 1N4735
- 4 1N914
- 1 OP999

Inductors

Qty. Description

- 1 1 mH
- 3 1 μ H
- 2 10 μ H
- 2 100 μ H
- 2 1000 μ H
- 2 10,000 μ H

Other

Qty. Description

- 1 Buzzer/speaker
- 1 630-tie solderless breadboard
- 1 Screwdriver: flathead
- 30 Jumper wires with pin ends



[coilcraft.com/
students](http://coilcraft.com/students)